

Face Spanners, With Pins

adjustable



9535



Material

Special steel, brown finish tempered.

Technical Notes

Fixed pin spot welded. For replacement pins see part no. 9536 page 833.

Tips

X is preferred size.
* Pin size equals stated size -0.1mm, tolerance h12.




Order No.	Type	Size					
			*				g
9535.W041	Fixed Pin	18 - 40	3,0x	4,0	150	5,0	90
9535.W042	Fixed Pin	18 - 40	4,0	5,0	150	5,0	90
9535.W081	Fixed Pin	40 - 80	4,0x	5,0	220	6,0	245
9535.W082	Fixed Pin	40 - 80	5,0	6,0	220	6,0	245
9535.W083	Fixed Pin	40 - 80	6,0	7,0	220	6,0	245
9535.W125	Fixed Pin	80 - 125	6,0x	7,0	295	8,0	615
9535.W126	Fixed Pin	80 - 125	7,0	7,5	295	8,0	615
9535.W127	Fixed Pin	80 - 125	8,0	8,0	295	8,0	615
9535.W201	Fixed Pin	125 - 200	8,0x	8,0	405	10,0	1530
9535.W202	Fixed Pin	125 - 200	10,0	10,0	405	10,0	1530
9535.W541	Replaceable Pin	18 - 40	3,0	4,0	150	5,0	90
9535.W542	Replaceable Pin	18 - 40	4,0	5,0	150	5,0	90
9535.W581	Replaceable Pin	40 - 80	4,0	5,0	220	6,0	245
9535.W582	Replaceable Pin	40 - 80	5,0	6,0	220	6,0	245
9535.W583	Replaceable Pin	40 - 80	6,0	7,0	220	6,0	245
9535.W625	Replaceable Pin	80 - 125	6,0	7,0	295	8,0	615
9535.W626	Replaceable Pin	80 - 125	7,0	7,5	295	8,0	615
9535.W627	Replaceable Pin	80 - 125	8,0	8,0	295	8,0	615
9535.W701	Replaceable Pin	125 - 200	8,0	8,0	405	10,0	1530
9535.W702	Replaceable Pin	125 - 200	10,0	10,0	405	10,0	1530

Replacement Pins

for face spanners 9402 and 9535



9536



Order No.	For 9402	For 9402	For 9535	Ø D*	L	M
9536.W002	.W061	-	.W541	3,0	4,0	M 4
9536.W003	.W062	-	.W542	4,0	5,0	M 4
9536.W004	.W063	-	-	5,0	6,0	M 4
9536.W007	-	-	.W581	4,0	5,0	M 5
9536.W008	-	-	.W582	5,0	6,0	M 5
9536.W009	-	-	.W583	6,0	7,0	M 5
9536.W011	-	.W101	-	5,0	6,0	M 6
9536.W012	-	.W102	.W625	6,0	7,0	M 6
9536.W013	-	-	.W626	7,0	7,5	M 6
9536.W014	-	.W103	.W627	8,0	8,0	M 6
9536.W017	-	-	.W701	8,0	8,0	M 8
9536.W019	-	-	.W702	10,0	10,0	M 8

Technical Notes

* Pin size is equal to stated size - 0.1mm, tolerance h12.



HAND TOOLS