

# Hook Spanners, With Pin Nose

fixed



# 9545

Order No.	Nut dia.	Thread Size of Nut DIN 1816M				
9545.W014	12-14	-	2,0	2,0	110/3	25
9545.W018	16-18	6	2,5	2,5	110/3	25
9545.W022	20-22	8	2,5	2,5	110/3	25
9545.W028	25-28	10-12	3,0	3,0	136/4	55
9545.W032	30-32	14-16	4,0	3,0	136/4	55
9545.W036	34-36	18-20	4,0	3,5	170/5	100
9545.W042	40-42	22-24	4,0	3,5	170/5	100
9545.W050	45-50	26-30	5,0	4,0	206/6	165
9545.W055	52-55	32-35	5,0	4,0	206/6	165
9545.W062	58-62	38-42	5,0	5,0	240/7	270
9545.W075	68-75	45-50	6,0	5,0	240/7	270
9545.W090	80-90	52-60	6,0	6,0	280/8	410
9545.W100	95-100	62-70	8,0	6,0	280/8	410
9545.W115	110-115	72-80	8,0	8,0	335/10	610
9545.W130	120-130	85-90	8,0	8,0	335/10	610
9545.W146	135-145	95-100	8,0	8,0	380/10*	790
9545.W166	155-165	105-120	8,0	8,0	380/10*	790
9545.W196	180-195	125-140	10,0	8,0	470/10*	1500
9545.W221	205-220	150-160	10,0	8,0	470/10*	1580
9545.W246	230-245	170-180	10,0	10,0	568/10*	2250
9545.W271	260-270	190-200	10,0	10,0	568/10*	2250

**Material**

Special steel, hardened and blackened. Edgewise ground.

**Technical Notes**

Specials available on request, including stainless steel models - subject to minimum quantities.

**Tips**

Items marked \*, thickness varies from DIN Standard. For round nuts with set pin holes to DIN 1816.



HAND TOOLS