



10160

STANDARD MANUAL CLAMPING

Material

Steel, heat-treated and blackened.

difficult to reach areas.

Technical Notes

The small nose permits clamping even on

Tips

„With thread“ for vertical adjustment.
„With slot“ for horizontal adjustment.

Used with:

21000 T-slot bolts, 24000 T-nuts, 24400 collar nuts, 25000 plain washer.

| Order No. | Type | l_1 | l_2 | l_3 | l_4 | l_5 | w_1 | w_2 | w_3 | h_1 | h_2 | h_3 | d_1 | Weight g |
|-------------|-------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|----------|
| 10160.W0107 | With thread | 80 | 34 | 23 | 17 | 13 | 15 | 6.6 | 7.5 | 8 | 2.5 | - | M 6 | 54 |
| 10160.W0109 | With thread | 100 | 42 | 29 | 22 | 17 | 20 | 9.0 | 9.5 | 12 | 4.0 | - | M 8 | 133 |
| 10160.W0111 | With thread | 125 | 52 | 36 | 28 | 21 | 25 | 11.0 | 11.5 | 15 | 5.0 | - | M10 | 261 |
| 10160.W0113 | With thread | 150 | 63 | 43 | 34 | 25 | 30 | 13.0 | 13.5 | 20 | 7.0 | - | M12 | 504 |
| 10160.W0117 | With thread | 175 | 70 | 52 | 40 | 29 | 35 | 17.0 | 15.5 | 25 | 9.0 | - | M16 | 828 |
| 10160.W0207 | With slot | 80 | 34 | 23 | 17 | 13 | 15 | 6.6 | 7.5 | 8 | 2.5 | 2.5 | - | 50 |
| 10160.W0209 | With slot | 100 | 42 | 29 | 22 | 17 | 20 | 9.0 | 9.5 | 12 | 4.0 | 3.0 | - | 127 |
| 10160.W0211 | With slot | 125 | 52 | 36 | 28 | 21 | 25 | 11.0 | 11.5 | 15 | 5.0 | 3.5 | - | 251 |
| 10160.W0213 | With slot | 150 | 63 | 43 | 34 | 25 | 30 | 13.0 | 13.5 | 20 | 7.0 | 4.0 | - | 488 |
| 10160.W0217 | With slot | 175 | 70 | 52 | 40 | 29 | 35 | 17.0 | 15.5 | 25 | 9.0 | 4.5 | - | 812 |
| 10160.W0222 | With slot | 225 | - | 62 | 52 | 33 | 50 | 22.0 | 19.5 | 35 | 15.5 | 5.5 | - | 2200 |
| 10160.W0226 | With slot | 250 | - | 71 | 60 | 36 | 60 | 26.0 | 21.5 | 40 | 17.5 | 5.5 | - | 3340 |

