



Goose Neck Clamps

Standard Manual Clam-



10200

STANDARD MANUAL CLAMPING

Material

Steel, heat-treated and enamelled.

() = not to DIN standard.

collar nuts, 25000 plain washer.

Technical Notes

To DIN 6316.

Tips

Used with:

21000 T-slot bolts, 24000 T-nuts, 24400

Order No.	For bolt	For bolt inch	l_1	l_2	l_3	l_4	w_1	w_2	w_3	h_1	h_2	h_3	Weight g
10200.W0007	M 6	1/4"	60	22.0	20	8	20	10	6.6	20	10	9	81
10200.W0009	M 8	5/16"	80	27.5	25	9	25	12	9.0	24	12	11	166
10200.W0011	M10	3/8"	100	36.0	32	12	30	15	11.0	30	15	14	299
10200.W0014	M12, M14	1/2"	125	44.0	40	16	40	20	14.0	40	20	18	678
10200.W0018	M16, M18	5/8"	125	51.5	40	20	50	25	(18.0)	50	25	23	1049
10200.W0019	M16, M18	5/8"	160	51.5	50	20	50	25	18.0	50	25	23	1366
10200.W0022	M20, M22	3/4"	160	59.0	55	24	60	30	(22.0)	60	30	27	1911
10200.W0023	M20, M22	3/4"	200	59.0	70	24	60	30	22.0	60	30	27	2417
10200.W0026	M24	1"	200	76.5	60	25	70	35	(26.0)	70	35	32	3315
10200.W0027	M24	1"	250	76.5	80	25	70	35	26.0	70	35	32	4132
10200.W0034	M30	1-1/4"	250	96.0	80	40	80	40	(33.0)	80	40	45	5225
10200.W0035	M30	1-1/4"	315	96.0	100	40	80	40	33.0	100	50	45	8459
10200.W0043	M36, M42	1-1/2" - 1-5/8"	400	105.0	120	50	100	50	(43.0)	120	60	55	17078

