




10100

Material

Steel, heat-treated and enamelled.

() = Not to DIN standard.

24000 T-nuts, 24400 collar nuts,
25000 plain washer.

Technical Notes

To DIN 6315B.

Tips

Used with:

26000 clamp support, 21000 T-slot bolts,

Order No.	For bolt	For bolt inch	l_1	w_1	w_2	w_3	h_1	h_2	Weight g
10100.W0007	M 6	1/4"	60	19	6.6	6	12	3	60
10100.W0009	M 8	5/16"	80	25	9.0	8	15	4	140
10100.W0011	M10	3/8"	100	31	11.0	10	20	5	300
10100.W0014	M12, M14	1/2"	125	38	14.0	12	25	6	570
10100.W0015	M12, M14	1/2"	160	38	14.0	12	25	6	730
10100.W0016	M12, M14	1/2"	200	38	14.0	12	25	6	910
10100.W0018	M16, M18	5/8"	160	48	18.0	15	30	8	1080
10100.W0019	M16, M18	5/8"	200	48	18.0	15	30	8	1360
10100.W0020	M16, M18	5/8"	250	48	18.0	15	40	10	2250
10100.W0022	M20, M22	3/4"	200	52	22.0	15	40	10	1800
10100.W0023	M20, M22	3/4"	250	62	22.0	20	40	10	3000
10100.W0024	M20, M22	3/4"	315	62	22.0	20	40	10	3850
10100.W0025	M20, M22	3/4"	500	62	(22.0)	20	50	10	7500
10100.W0026	M24	1"	200	66	26.0	20	40	10	2400
10100.W0027	M24	1"	250	66	26.0	20	40	10	3000
10100.W0028	M24	1"	315	66	26.0	20	40	10	3850
10100.W0029	M24	1"	400	66	(26.0)	20	50	10	5962
10100.W0030	M24	1"	500	66	(26.0)	20	50	10	7600
10100.W0031	M24	1"	600	66	(26.0)	20	50	10	9042
10100.W0032	M24	1"	800	66	(26.0)	20	50	10	12122
10100.W0034	M30	1-1/4"	250	74	33.0	20	50	12	3700
10100.W0035	M30	1-1/4"	315	74	33.0	20	50	12	4750
10100.W0036	M30	1-1/4"	400	74	33.0	20	50	12	6100
10100.W0037	M30	1-1/4"	600	74	(33.0)	20	50	12	9200
10100.W0038	M30	1-1/4"	1000	94	(33.0)	30	60	12	28000
10100.W0040	M36	1-1/2"	400	100	(40.0)	30	60	12	11000
10100.W0041	M36	1-1/2"	600	100	(40.0)	30	60	12	16500
10100.W0042	M36, M42	1-5/8"	600	123	(43.0)	40	80	12	29600

