




10164

STANDARD MANUAL CLAMPING

Material

Stainless steel (AISI 630, 17-4 PH), heat-treated.

both normal and restricted areas with minimum tooling interference.

collar nuts, 25000 plain washer.

Technical Notes

This is a low profile slotted clamp for use in

Tips

Used with:
21000 T-slot bolts, 24000 T-nuts, 24400

Order No.	Type	Holding force kN	l_1	l_2	w_1	w_2	h_1	d_1	Weight g
10164.W0092	One	14.2	92	22.0	22.6	10.4	11	9,5 Ø	150
10164.W0127	Two	26.7	127	34.5	25.4	13.4	19	M12	340
10164.W0152	Two	38.2	152	38.1	30.5	16.5	22	M16	600
10164.W0178	Two	69.8	178	38.1	35.6	19.8	27	M20	1130