


Stepped Clamp with adjusting support screw

Standard
Manual Clam-



10230

STANDARD MANUAL CLAMPING

Material

Steel, heat-treated and enamelled.

Technical Notes

To clamp thin parts, turn the clamp over.

Order No.	For clamping screw	$d_1 \times l_2$	l_4	l_5	w_1	$w_2 \times l_1$	h_1	h_2	$h_3 \times l_3$	Weight g
10230.W0014	M12, M14	M12x49	40	21	40	14x100	10-55	20	8,0x10,0	580
10230.W0018	M16, M18	M16x55	45	26	50	18x125	13-62	25	10,0x12,5	1140
10230.W0022	M20, M22	M20x69	60	30	60	22x160	16-77	30	12,0x15,0	2100