




Stepless Adjustable Clamps

Adjustable Vertical Clamps



10620

ADJUSTABLE VERTICAL CLAMPS

Material

Steel, tempered and galvanised.

body has a long slot for easy positioning.

Technical Notes

Ideal for press tool clamping. The clamp

Tips

Supplied without T-bolt or nut - for these parts see nos. 21000 and 24400.

Order No.	Clamping height h_1 min. max.	For T-slot	For bolt	h_2 min. max.	l_2	l_3	l_4	l_5	$w_1 \times l_1$	d_1	Weight g
10620.W0012	0-35	12 & 14	M12	30-55	48	28	23	14	38x88	13	260
10620.W0016	0-55	16 & 18	M16	42-84	74	38	29	18	56x130	18	809
10620.W0020	0-65	20 & 22	M20	50-100	80	46	32	20	66x140	22	1253
10620.W0026	0-75	24 & 28	M24	54-111	100	52	39	24	76x174	26	1718
10620.W0032	0-80	36	M30	62-125	110	61	44	28	90x200	32	2785

