



## 10588.3

STANDARD MANUAL CLAMPING

### Material

Steel, tempered, alloyed and galvanised (black).

### Technical Notes

Complete with three-step support element, clamping unit and mounting kit.

### Tips

Three step clamping:

1. Position clamp on table and tighten to correct torque.
2. Adjust the clamping arm.
3. Tighten the clamping screw to clamp

part (tighten to correct torque).

### Important Notes

**Not suitable for use on injection moulding, die casting machines or presses.**

Order No.	Size	For T-slot	d <sub>1</sub>	d <sub>3</sub>	d <sub>5</sub>	h <sub>1</sub> min.   max.	h <sub>2</sub>	h <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>	Torque to d <sub>2</sub> Nm max.	Torque to d <sub>4</sub> Nm max.	w <sub>1</sub>	w <sub>2</sub>	w <sub>3</sub>	A/F	Load capacity for static load kN max.	Weight g
<b>10588.W0222</b>	22	14	M12	40	M12	9-74	98	67	65	30-58	13,5	55	52	13	14,5	6	22	1120
<b>10588.W0230</b>	30	14	M12	70	M16	13-129	146	101	130	37-106	13,5	100	68	18	22,5	8	30	4600
<b>10588.W0243</b>	43	18	M16	150	M20	16-147	175	116	150	48-114	17,5	200	75	20	25,0	10	43	6844
<b>10558.W0249</b>	49	22	M20	200	M24	16-169	207	140	170	68-172	22,0	220	85	25	29,0	12	49	10870