


# Clamp - Plastic Cover

## Adjustable Vertical Clamps



**10630.1**

ADJUSTABLE VERTICAL CLAMPS

### Material

Steel, tempered and burnished.

### Technical Notes

Weight-saving thanks to its lightweight design. Variable and fast adjustment at a distance from the workpiece. No additional

clamping supports are needed to reach the required clamping height. The U-piece is undetachable from the clamp.

### Tips

For clamping, clamping bolts no. 21000 and studs no. 21100 and cheese head

screws (ISO 4762) can be used.

A washer no. 25000 must always be used between the hexagonal nut and U-piece.  $h_1$  is dependent on depth of slot to DIN 650 and position of fixture nut.

| Order No.   | Size | For clamping screw | $h_1$<br>min./max. | $h_2$ | $h_3$ | $l_1$ | $l_2$ | $l_3$ | $w_1$ | $d_1$ | Weight<br>g |
|-------------|------|--------------------|--------------------|-------|-------|-------|-------|-------|-------|-------|-------------|
| 10630.W0010 | 10   | M10                | 0-15               | 32.0  | 30.5  | 80    | 30    | 19    | 44    | 11    | 257         |
| 10630.W0014 | 14   | M12-M14            | 0-33               | 49.5  | 47.0  | 125   | 37    | 51    | 57    | 14    | 708         |
| 10630.W0018 | 18   | M16-M18            | 0-45               | 62.0  | 58.5  | 160   | 49    | 63    | 67    | 18    | 1235        |
| 10630.W0022 | 22   | M20-M22            | 0-65               | 75.0  | 71.5  | 200   | 58    | 63    | 72    | 22    | 1880        |
| 10630.W0026 | 26   | M22-M24            | 0-85               | 94.0  | 89.5  | 250   | 74    | 0     | 82    | 16    | 2799        |

