



10600

ADJUSTABLE VERTICAL CLAMPS

Material

Steel, forged, tempered and burnished.

Technical Notes

Type one: clamp and T-bolt set.

Type two: clamp only.

h_1 - depends on the depth of the slot position and the position of the fixture nut.

Tips

Often used for clamping press tools.

Easy height adjustable clamp. No fitting

support required.

Used with:

21000 T-slot bolts, 24400 collar nuts,

25000 plain washer.

Order No.	Type	T-bolt	For T-bolt	For T-slot	$d_1 \times l_1$	h_1	l_2	l_3	l_4	l_5	w_1	Weight g
10600.W0012	Clamp set	M12x12x125	M12 - M16	12	17x140	0-50	110	60	55	30	50	1070
10600.W0014	Clamp set	M12x14x125	M12 - M16	14	17x140	0-50	110	60	55	30	50	1080
10600.W0016	Clamp set	M16x16x160	M12 - M16	16	17x140	0-75	110	60	55	30	50	1270
10600.W0018	Clamp set	M16x18x160	M12 - M16	18	17x140	0-75	110	60	55	30	50	1280
10600.W0020	Clamp set	M20x20x200	M18 - M20	20	21x175	0-85	135	80	70	40	60	2300
10600.W0022	Clamp set	M20x22x200	M18 - M20	22	21x175	0-85	135	80	70	40	60	2370
10600.W0117	Clamp only	-	M12 - M16	-	17x140	0-75	110	60	55	30	50	900
10600.W0121	Clamp only	-	M18 - M20	-	21x175	0-85	135	80	70	40	60	1600

