



10630.1

ADJUSTABLE VERTICAL CLAMPS

Material

Steel, tempered and burnished.

Technical Notes

Weight-saving thanks to its lightweight design. Variable and fast adjustment at a distance from the workpiece. No additional

clamping supports are needed to reach the required clamping height. The U-piece is undetachable from the clamp.

Tips

For clamping, clamping bolts no. 21000 and studs no. 21100 and cheese head

screws (ISO 4762) can be used.

A washer no. 25000 must always be used between the hexagonal nut and U-piece. h_1 is dependent on depth of slot to DIN 650 and position of fixture nut.

Order No.	Size	For clamping screw	h_1 min. max.	h_2	h_3	l_1	l_2	l_3	w_1	d_1	Weight g
10630.W0010	10	M10	0-15	32.0	30.5	80	30	19	44	11	257
10630.W0014	14	M12-M14	0-33	49.5	47.0	125	37	51	57	14	708
10630.W0018	18	M16-M18	0-45	62.0	58.5	160	49	63	67	18	1235
10630.W0022	22	M20-M22	0-65	75.0	71.5	200	58	63	72	22	1880
10630.W0026	26	M22-M24	0-85	94.0	89.5	250	74	0	82	16	2799

