


T-Slot Finger Clamp Set

low profile



10960



Material

Clamp: spring steel.
Block: steel.

Technical Notes


The clamping point is 5mm above the machine table. Risers can be used to allow for through machining and drilling.

Supplied as a set: one-piece clamp, one-piece stop.

Tips

These low-profile clamps and stops have a holding force of 4000 N. The fingers push the workpiece down before clamping. The small height of the clamps eliminate any risk of collision between clamp and tooling- ideal for machining small and low profile components.

Order No.	Type	For T-slot	Clamping height min.	Clamping stroke s_1	h_1	h_2	h_3	l_1	l_2	w_1	w_2	A/F	Torque to max. Nm.	Max. clamping force kN.	g
10960.W0260	Clamp + Stop	10	5	1,2	10,5	7,5	5	46	15	18	20	4	9	4	140
10960.W0262	Clamp + Stop	12	5	1,2	10,5	7,5	5	48	15	18	20	4	9	4	150
10960.W0264	Clamp + Stop	14	5	1,2	10,5	7,5	5	52	15	22	20	4	9	4	162
10960.W0266	Clamp + Stop	16	5	1,2	10,5	7,5	5	48	15	25	20	4	9	4	178
10960.W0268	Clamp + Stop	18	5	1,2	10,5	7,5	5	48	15	25	20	4	9	4	190




workpiece supported on the table or raised with a wedge.
(for through-hole machining)

T-Slot Finger Clamp Set

low profile



10960



Material

Clamp: spring steel.
Block: steel.

Technical Notes

The clamping point is 5mm above the machine table. Risers can be used to allow for through machining and drilling.

Supplied as a set: one-piece clamp, one-piece stop.

Tips

These low-profile clamps and stops have a holding force of 4000 N. The fingers push the workpiece down before clamping. The small height of the clamps eliminate any risk of collision between clamp and tooling- ideal for machining small and low profile components.