


## **Piccolo Clamp Sets**





10657

## **Technical Notes**

Comprises of two piccolo clamping elements (short 10655.W0020 and long

10655.W0025), two spacer elements (2 x 10656.W0030), one clamping key (10656.W0180), one extra long arm, four M10

screws and six M10 T-nuts (with spring) for 14, 16 and 18mm slots.

Order No.	Description	Clamp reach	Clamping force kN	Clamping height min.   max.
			max.	
10657.W0100	Piccolo Clamp Set	54	6.5	0 to 118



## A Wide Range of Clamps to Match any Requirement




















2



## **Monobloc Clamps**

stackable vertical clamping







Slide the T-nut into the T-slot position and tighten the clamp onto the T-slot base, with the aid of the clamp key (shown in the image in blue.

Clamp the workpiece by twisting the key. Start machining.


When unclamped the arm and the clamp remain in position



Fix to threaded bases with a special screw M10, M12, M14, M16.



Fix to T-slots with suitable T-nuts.



The clamps are easily stackable to achieve required clamping height.



ov-W10650-A-T-stackable-clamps-rnh - Updated - 20-10-2022