



10990

LOW PROFILE SIDE CLAMPING

Material

Body: steel (42CrMo), tempered. Black oxide finish.

Jaw: steel (42CrMo), tempered, black oxide finish. Precision ground (smooth jaw).

Order No.	Type	d ₁	l ₁	l ₂	h ₁	h ₂	h ₃	h ₄	w ₁	w ₂	w ₃	s ₁	Torque to Nm max.	A/F	Clamping force kN max.	Weight g
10990.W0025	Serrated	M 8	39.5	25	16	19.5	1.5	7	65	25	45	7	8	4	4	180
10990.W0035	Serrated	M12	60.0	40	22	29.0	2.0	9	85	35	60	12	26	6	9	500
10990.W0040	Serrated	M16	77.0	50	30	38.0	2.0	13	100	40	70	14	60	8	17	1010
10990.W0125	Smooth	M 8	39.5	25	16	19.5	1.5	7	65	25	45	7	8	4	4	180
10990.W0135	Smooth	M12	60.0	40	22	29.0	2.0	9	85	35	60	12	26	6	9	510
10990.W0140	Smooth	M16	77.0	50	30	38.0	2.0	13	100	40	70	14	60	8	17	1020