


2.2 Ton Finger Clamp - Fixed Stop

smooth face

Heavy-Duty Side Clamping



Tips

Material


Spring steel.

Technical Notes

These stops have a unique sideways and downwards action.

Provided with specially ground location bolts \emptyset 10,2 - M10, allowing for precise positioning. Precision of the screws also allows dimension l_2 to be used as a useful clamping datum. For mounting there are 2 tapped holes at 44,00 ±0,005mm centres, M10, with depth of 28mm, counterbore 10,2 (H6), with depth of 14mm.

| Order No. | Туре | Clamping height h_1 | d_1 | d ₂ tol. h6 | h ₂ | h ₃ | I_1 | I ₂ | w_1 | w ₂ |
|-------------|--------|-----------------------|-------|---------------------------|----------------|----------------|-------|----------------|-------|----------------|
| 11041.W0080 | Single | 7 | M10 | 10.2 | 22 | 15 | 50 | 30 | 60 | 44 |
| 11041.W0082 | Double | 7 | M10 | 10.2 | 22 | 15 | 60 | 30 | 60 | 44 |





HEAVY-DUTY SIDE CLAMPING

Horizontal Clamping

up to 2.2 tons



Clamping Torque



| 11040/CL2040 | | | | |
|----------------|--|--|--|--|
| Clamping Force | | | | |
| Ν | | | | |
| 23000 | | | | |
| 18000 | | | | |
| 12500 | | | | |
| 11500 | | | | |
| 9500 | | | | |
| | | | | |



| 11070/CL2070 | | | | |
|-----------------|-----------------------|--|--|--|
| Clamping Torque | Clamping Force | | | |
| N/m | Ν | | | |
| 60 | 16500 | | | |
| 50 | 15000 | | | |
| 40 | 12000 | | | |
| 30 | 10000 | | | |
| 25 | 8000 | | | |
| 20 | 7000 | | | |



| 11081/CL2081 | | | | |
|-----------------|----------------|--|--|--|
| Clamping Torque | Clamping Force | | | |
| N/m | Ν | | | |
| 5 | 6600 | | | |
| 4.5 | 5500 | | | |
| 4 | 4900 | | | |

wixroyd.com



Clamping Torque

N/m

8.5

8 7

6

5

4

ov-W11040-A-T-W10940-A-T-horizontal-clamping-lnh- Updated -13-10-2022






Mini Finger Clamps Application



Application



Unique Horizontal Clamping Set-Ups







Unique Horizontal Clamping



Unique Action - "three finger" Clamping

Pull down AND clamp with the highest of clamping forces – from 0,4 tons to 2,2 tons! Used in our clamping series:


10900, 10940, 10880, 10920, 11040, 11041, 11042, 11043, 11070, 11071, 11080, 11081, 11082, 11083

HEAVY-DUTY SIDE CLAMPING

Our horizontal clamps have a unique "three finger" arrangement ensuring components are both pulled down and clamped in the same motion. The face of the clamp is made of three parts or "fingers":

- Two outer flexible fingers (1); for pulling down the component to the work table.
- One solid central finger (2), to provide direct clamping action.

Available in two styles – smooth and serrated face. They can also cater for workpieces with an adverse angle on the clamping face – for example flame cut steel blanks.




Clamping Action

| Contact | The clamps outer flexible fingers 1 are approx. 0,25mm longer than the solid central finger/ clamping stop 2, this slight difference in length means it is the flexible fingers which first come into contact with the workpiece. As initial contact is made with the work-piece the flexible fingers 1 apply downward pressure forcing the workpiece down against the work table, the flexible fingers are compressed until they are the same length as the solid central finger/clamping stop 2. | view exaggerated for demonstration |
|-----------|---|---|
| Clamping | As the solid central finger/clamping stop 2 comes into contact with the work-piece it applies high side clamping pressure to achieve clamping forces up to 2,2 tons (dependent upon clamping model selected). | workpiece 2 clamp t clamping pushdown |
| Machining | During machining the uniquely designed flexible fingers 1 continue to flex and twist applying downward pressure to keep the workpiece flat to the work table throughout. | workpiece continual flex and pushdown |

Precision Positioning

The unique clamping action achieves precision positioning of workpieces – ensuring the workpiece remains parallel to the reference surface.



throughout machining







Horizontal Clamping

up to 2.2 tons


Clamping & Height Setting

Unique Action - "three finger" Clamping


Our horizontal clamps have a unique "three finger" arrangement ensuring components are both pulled down and clamped in the same motion. The face of the clamp is made of three parts or "fingers":

- Two outer flexible fingers (1); for pulling down the component to the work table.
- One solid central finger (2), to provide direct • clamping action.


Available in two styles – smooth and serrated face. They can also cater for workpieces with an adverse angle on the clamping face - for example flame cut steel blanks.








Options




Quick 1/4 turn eccentric clamping - on models offering 4000 and 12000 Newtons clamping force.




T-Slotted tables

ov-W10920-A-T-W10940-c-rnh - Updated - 21-10-2022

Dedicated fixturing



Rear screw clamping - on models offering 6500, 10000 and 22000 Newtons clamping force.



Mounting

Actuation

Modular fixturing



sales@wixroyd.com