




10982.1

LOW PROFILE SIDE CLAMPING

Material

Body: steel (C45), black oxide finish.
Jaw: steel (42CrMo), tempered. Black oxide finish. Precision ground.
Shaft: steel (42CrMo), black oxide finish.

long clamping stroke and firm clamping. The precision-ground jaw is perfect for clamping the workpiece on its finished surface. The jaw provides downward force to prevent part lift.

Tips

Can be clamped with both hex wrench and spanner.

Technical Notes

A screw type clamping mechanism allows a

Order No.	Clamping stroke s_1	d_1	d_2	d_3	l_1	l_2	l_3	l_4	l_5	l_6	h_1	h_2	h_3	Weight g
10982.W0045	3	6.6	M 4x0,7 Depth 6	M 4x0,7-6L	52	48	20	14	3	10	32	27	18	560
10982.W0060	4	8.6	M 5x0,8 Depth 8	M 5x0,8-8L	69	63	26	19	4	13	40	33	22	1240

Order No.	h_4	h_5	h_6	w_1	w_2	w_3	w_4	w_5	s_2	Torque to Nm max.	A/F_1	A/F_2	Clamping force kN max.
10982.W0045	18	18	8	75	45	15	60	30	3	25	8	19	9
10982.W0060	22	22	10	100	60	20	80	40	4	50	10	24	14

