





Clamping Module - Single flanged

Bore Clamping



12043

BORE CLAMPING

Material

Steel (AISI 4140), induction hardened, black oxide finish.

Technical Notes

For suitable clamping screws see part no.s

12046 through 12050.

For permissible cutting forces and corresponding workpiece weights when using the clamping module system, see technical pages.

Order No.	h_1 ± 0.01	h_2	h_3	l_1	w_1	Type	Size	d_1	d_2	d_3	d_4	h_4	A/F	Clamping force kN max.	Screw torque Nm max.	Weight g
12043.W0008	25	12.5	12.5	42	54	One	8	30	34.5	15	6.6	7	3	5	4	100
12043.W0011	40	20.0	20.0	50	65	Two	11	40	46.0	22	9.0	10	4	8	8	300
12043.W0016	63	33.0	30.0	75	95	Two	16	60	69.0	32	13.0	15	6	15	50	1400
12043.W0021	80	40.0	40.0	100	130	Two	21	80	91.0	44	17.0	20	8	25	50	3300