



Modular Pitbull Clamps



Low Profile Side Clamping



12033.2

LOW PROFILE SIDE CLAMPING

Material

Hardened and ground steel bodies with pitbull clamps insert (part no. 12031).

Technical Notes

Designed to be used in fixtures, on cubes etc.

The slotted version has a clamp step to

support the workpiece off the machine table for through milling or drilling.

The height of the clamp can be adjusted by varying the depth of the milled slot used to locate the clamp.

Tips

The compact version is ideal for clamping

workpieces in series, using the back surface of the clamp to locate the next workpiece.

Back of clamp is ground square to the bottom for precise part location.

Order No.	Clamp type	d_1	h_1	l_1	l_2	w_1	Grip height	Replacement clamps
12033.W0150	Versagrip	M12	35	76.2	50	25.4	1,5 to 3,0	12036.W0175
12033.W0155	Talongrip	M12	35	76.2	50	25.4	1,5 to 3,0	12034.W0050
12033.W0160	Pitbull - Knife	M12	35	76.2	50	25.4	6.4	12031.W0060
12033.W0165	Pitbull - Blunt	M12	35	76.2	50	25.4	6.4	12031.W0070
12033.W0170	Pitbull - Mach.	M12	35	76.2	50	25.4	6.4	12032.W0570