


Variable Hexagon Clamps low height







12040

Material

Body: steel, hardened and blackened. Screw: steel, eccentric, heat treated (10,9) and blackened.

Technical Notes

Hexagon clamps actuated by means of an

eccentric screw (provided). Available with either smooth or ribbed faces.

Tips

Max. clamping section is 25mm. Each of the clamp's faces increases the distance from the centre line by 1mm, thus workpieces of varying sizes can be held using just one clamp and is actuated by a simple rotation of the clamp face.

Reorder screw 12112.W0512.

Order No.	Finish	h_1	I_1	Clamp stroke	Clamping force kN max.	Weight g
12040.W0002	Clamp, smooth	22	12 - 17	2	18	100
12040.W0004	Clamp, smooth	22	18 - 23	2	18	132
12040.W0006	Clamp, smooth	22	24 - 29	2	18	204
12040.W0008	Clamp, smooth	22	30 - 35	2	18	299
12040.W0012	Clamp, ribbed	22	12 - 17	2	18	77
12040.W0014	Clamp, ribbed	22	18 - 23	2	18	132
12040.W0016	Clamp, ribbed	22	24 - 29	2	18	204
12040.W0018	Clamp, ribbed	22	30 - 35	2	18	299

