



### 12100

LOW PROFILE SIDE CLAMPING

#### Material

Steel, heat-treated, blackened.

The clamps produce a downwards and forwards clamping force.

up to dimension „w<sub>2</sub>“, via grinding.  
**Sold in pairs.**

#### Technical Notes

Ideal for clamping low profile plates.

#### Tips

The clamp height can be further reduced by

Order No.	Slot size	F <sub>1</sub> kN	F <sub>2</sub> kN	l <sub>1</sub> max.	h <sub>1</sub>	h <sub>2</sub> min.	h <sub>2</sub> max.	w <sub>1</sub>	w <sub>2</sub>	Stroke s <sub>1</sub>	Weight g
12100.W0012	12	5.0	0.6	52	11	2.5	13.5	18	5	1.8	300
12100.W0014	14	5.5	0.7	55	11	1.5	13.5	22	5	1.8	380
12100.W0016	16	8.0	0.9	68	15	2.5	17.0	25	6	2.5	700
12100.W0018	18	9.0	1.0	71	15	1.5	16.0	28	6	2.5	830
12100.W0022	22	16.0	1.9	89	20	4.5	21.5	35	9	3.0	1740

