


Eccentric Knife Edge Clamps

Low Profile Side Clamping



12120

LOW PROFILE SIDE CLAMPING

Material

Ribbed face steel, hardened and plated.
Screw steel hardened, strength class 10,9.

Technical Notes

For clamping workpieces with uneven

surfaces, this clamp provides serrations to help the clamp grip the workpiece.

Tips

Clockwise rotation is recommended. The workpiece should be to the right of the

clamp. For replacement cam screws see parts 12112.

Important Notes

w_1 is distance to drill and tap from edge of workpiece.

Order No.	d_1	d_2	h_1	l_1	Clamping force kN	Stroke s_1	w_1	A/F	Torque to Nm max.	Qty/pack	Weight g
12120.W0020	M10x1,5	20.60	6.35	19.0	8.8	1.22	10.2	7	28	8	40
12120.W0025	M12x1,75	25.40	9.52	22.8	17.7	2.03	12.7	8	88	8	45
12120.W0030	M16x2	30.15	12.70	28.5	26.6	2.54	15.0	12	135	4	90

