



12150

LOW PROFILE SIDE CLAMPING

Material

Clamp: brass.
Body: steel heat treated.

Tips

For replacement clamping screws see 12112.
Hex. key not included.
Sold in packs of 2.

Technical Notes

For use in T-slots of machine tables.

Order No.	For T-slot	Cam screw	l_1	h_1	h_2	h_3	w_1	w_2	Torque to Nm max.	Stroke s_1	A/F_1	A/F_2	Holding force kN
12150.W0008	8	M 6x1,00	23.2	9.5	4.8	4.6	12.7	8	8.5	1.01	5	15.9	3.5
12150.W0010	10	M 6x1,00	23.2	14.2	4.8	4.3	14.2	10	8.5	1.01	5	15.9	3.5
12150.W0012	12	M 8x1,25	27.9	15.9	4.8	6.4	15.9	12	11.3	1.01	5	20.6	3.3
12150.W0014	14	M10x1,50	30.5	22.2	6.4	8.5	22.4	14	28.0	1.52	7	20.6	8.9
12150.W0016	16	M12x1,75	30.9	22.2	9.5	9.2	25.4	16	61.0	2.03	8	25.4	13.3
12150.W0018	18	M12x1,75	34.7	28.6	9.5	10.5	28.6	18	61.0	2.03	8	25.4	13.3
12150.W0020	20	M16x2,00	39.2	31.8	12.7	12.6	31.8	20	135.0	2.54	12	30.2	26.7
12150.W0022	22	M16x2,00	44.3	41.3	12.7	12.5	34.9	22	135.0	2.54	12	30.2	26.7

