




# Clamping Jaws - Low Height downhold action

## Heavy-Duty Side Clamping



**12200**

HEAVY-DUTY SIDE CLAMPING

### Material

Steel, heat treated, blackened.

Acutated on one side via hex. key  
(provided).

wards into the workpiece.  
**Sold in pairs.**

### Technical Notes

Ideal for clamping low-profile plates.

### Tips

Clamping action is forwards and down-

| Order No.   | T-slot size | $w_1$ | $d_1$ | $h_1$ | $l_1$ | $l_2$ | $l_3$ | Stroke $s_1$ | $F_1$<br>kN | $F_2$<br>kN | Weight/pair<br>g |
|-------------|-------------|-------|-------|-------|-------|-------|-------|--------------|-------------|-------------|------------------|
| 12200.W0012 | 12          | 40    | M10   | 20    | 80    | 39    | 26    | 3            | 16          | 0.6         | 1150             |
| 12200.W0014 | 14          | 40    | M12   | 20    | 80    | 39    | 26    | 3            | 22          | 0.9         | 1250             |
| 12200.W0016 | 16          | 40    | M12   | 20    | 80    | 39    | 26    | 3            | 22          | 0.9         | 1330             |
| 12200.W0017 | 16          | 50    | M14   | 25    | 100   | 46    | 34    | 4            | 32          | 1.2         | 2340             |
| 12200.W0018 | 18          | 50    | M16   | 25    | 100   | 46    | 34    | 4            | 36          | 1.4         | 2540             |
| 12200.W0020 | 20          | 50    | M16   | 25    | 100   | 46    | 34    | 4            | 36          | 1.4         | 2660             |
| 12200.W0022 | 22          | 78    | M20   | 30    | 140   | 65    | 50    | 5            | 36          | 1.4         | 5980             |
| 12200.W0024 | 24          | 78    | M20   | 30    | 140   | 65    | 50    | 5            | 36          | 1.4         | 6330             |
| 12200.W0028 | 28          | 78    | M24   | 30    | 140   | 65    | 50    | 5            | 40          | 1.6         | 7060             |
| 12200.W0030 | 30          | 78    | M24   | 30    | 140   | 65    | 50    | 5            | 40          | 1.6         | 7580             |

