



12109

LOW PROFILE SIDE CLAMPING

Material

Steel (AISI 4140), HRc 33-39, blackened.

Technical Notes

Simple and robust cam clamp. Easy to

install. Actuated with spanner.

Tips

To install: insert flanged collar and locking screw into cam body. Tighten locking screw

to fix cam in position. Load component, then use spanner to turn and actuate cam to clamp up to workpiece surface.

Order No.	d_1	d_2	h_1	h_2	l_1	w_1	w_2	Stroke s_1	A/F_1	A/F_2	Torque to Nm max.	Clamping force kN max.	Weight g
12109.W0024	24	M 8x1,25	16	8	12	12	16.4	4.4	6	19	50	5.2	55
12109.W0030	30	M10x1,50	20	10	15	15	20.5	5.5	8	24	75	8.0	110
12109.W0034	34	M12x1,75	24	12	18	17	23.2	6.2	10	27	90	9.3	185

