




Low Profile Flat Clamps for T-slots

Heavy-Duty Side Clamping



12205

HEAVY-DUTY SIDE CLAMPING

Material

Steel, tempered and burnished.

Suitable for horizontal and vertical applications.

Technical Notes

Low height clampings of thin workpieces.

Tips

For clamping of low profile workpieces.

Order No.	T-slot size	w ₁	d ₁	h ₁ min.	h ₁ max.	h ₂	l ₁	l ₂	l ₃	F ₁ kN	F ₂ kN	Weight g
12205.W0014	14	15	M12	16	25	16	110	45-48	26	15	7.5	579
12205.W0016	16	15	M12	16	25	16	110	45-48	26	15	7.5	600
12205.W0018	18	20	M16	19	30	19	130	50-54	33	20	10.0	1011
12205.W0020	20	20	M16	19	30	19	130	50-54	33	20	10.0	1055
12205.W0022	22	30	M20	22	36	22	152	58-63	41	30	15.0	1670
12205.W0024	24	30	M20	22	36	22	152	58-63	41	30	15.0	1705
12205.W0028	28	30	M20	22	36	22	152	58-63	41	30	15.0	1807