



12428

LOW PROFILE SIDE CLAMPING

Material

Body: steel (C45), black oxide finish.
 Arm: steel (C45), tempered and black oxide finish.
 Jaw: steel (SKH51), tempered and black oxide finish.

Technical Notes

The jaw swivels to align to an unmachined surface of the workpiece. The jaw is replaceable.
 For mounting, use a cap screw to suit d_1

Tips

For replacement jaws, see part nos. 35520.W0303, 35520.W0306 and 35520.W0310.

Order No.	h_1	h_2	h_3	l_1	l_2	l_3	d_1	d_2	d_3	Stroke s_1	w_1	w_2	w_3	Clamping force kN max.	Torque to Nm max.	Weight g
12428.W0012	40	32	31	62.5	45	30	M 8	M 4x4	M 8x35	5.3	45	12	25	15	25	0.6
12428.W0016	50	40	39	74.0	55	40	M10	M 4x4	M10x40	7.1	55	16	30	27	50	1.0
12428.W0020	60	48	47	91.0	65	45	M12	M 5x5	M12x50	8.0	65	20	35	38	90	1.7

