




# Clamping Jaws - Standard downhold action

## Heavy-Duty Side Clamping



**12300**

HEAVY-DUTY SIDE CLAMPING

### Material

Body: cast iron.  
Jaws: steel, hardened.

### Technical Notes

For mounting of each clamp to machine

table, two clamping bolts no. 21000,  
washers no. 25000 and fixture nuts no.  
24300 should be ordered separately.  
Hex. key provided.

### Tips

Can be actuated from left hand side only.  
**Sold in pairs.**  
For table of clamping forces, see below.

| Order No.   | For T-slot | $w_1$ | $w_2$ | $h_1$ | $h_2$ | $h_3$ | $l_1$ | $l_2$ | Stroke $s_1$ | Weight<br>g |
|-------------|------------|-------|-------|-------|-------|-------|-------|-------|--------------|-------------|
| 12300.W0016 | 10-14      | 40    | 13    | 50    | 20    | 30    | 115   | 60    | 3            | 1590        |
| 12300.W0018 | 16-20      | 50    | 19    | 60    | 25    | 35    | 150   | 72    | 4            | 2940        |
| 12300.W0030 | 22-36      | 80    | 31    | 75    | 30    | 45    | 205   | 102   | 5            | 7900        |

