




Hook Clamps low height



Adjustable Vertical Clamps



12550.1

ADJUSTABLE VERTICAL CLAMPS

Material


Steel (42CrMo), tempered, black oxide finish.

Technical Notes

Very useful for limited space vertical clamping, can be recessed into bores to minimise height. Clamping stroke (see diagram below) for M 4= 0-3mm, for M 6= 0-4mm.

Clamping stroke (see diagram below) for M 4= 0-3mm, for M 6= 0-4mm.

Order No.	h_1	l_1	d_1 -0.02 -0.10	d_2	h_2	h_3	h_4	d_3	l_2	l_3	w_1	w_2	Torque to Nm max.	A/F	Clamping force kN max.	Weight g
12550.W0010	24,5	14	10	M 4x0,7	14,5	7,5	12,5	M 4x30	18	8	8	14	2,7	3	2,0	25
12550.W0012	30,5	17	12	M 5x0,8	17,5	9,5	13,5	M 6x35	22	10	10	16	7,0	5	3,5	45



installation dimensions into custom base plate