




Cam Edge Clamps

Low Profile Side Clamping



12426

LOW PROFILE SIDE CLAMPING

Material

Body/jaw: steel (42CrMo), tempered and black oxide finish.

Cam: steel (C45), tempered and black

oxide finish.

Technical Notes

Secure the body and the flanged collar

with a socket head cap screw. Turn the cam with a wrench to clamp a workpiece.

Order No.	h_1	h_2	h_3	h_4	h_5	l_1	l_2	l_3	d_1	Stroke s_1	w_1	w_2	w_3	A/F	Clamping force kN max.	Torque to Nm max.	Weight g
12426.W0032	20	23	8	7	15	44	28,5	26,5	M 8x30	4,0	32	19	10	6	3,5	45	160
12426.W0040	25	29	10	9	16	54	35,0	33,0	M10x35	5,0	40	24	12	8	5,5	55	310
12426.W0046	30	35	12	11	17	62	39,5	37,5	M12x40	5,5	46	27	14	10	7,0	70	490

