




Hook Clamp flanged



Adjustable Vertical Clamps



12550.3

ADJUSTABLE VERTICAL CLAMPS

Material

Steel (42CrMo), quenched and tempered, black oxide finish.

Holder: steel (C45), quenched and

tempered, black oxide finish.

Technical Notes

Ideal for low height clamping.

The hook clamp is designed to move up and down in conjunction with the tightening screw.

Order No.	h_1	Stroke s_1	l_1	d_1	d_2	h_2	h_3	h_4	h_5	Weight g
12550.W0210	6	3	14	4.3	M 4x0,7	16	7.5	16	11	45
12550.W0212	8	4	17	5.3	M 5x0,8	19	9.5	19	12	75

Order No.	h_6	d_3	l_2	l_3	w_1	w_2	w_3	w_4	Torque to Nm max.	A/F	Clamping force kN
12550.W0210	26	M 4x30	18	14	8	14	24	34	2.7	3	2.0
12550.W0212	32	M 5x35	22	16	10	16	28	40	7.0	5	3.5

