




Hook Clamps spring loaded

Adjustable Vertical Clamps



12552

ADJUSTABLE VERTICAL CLAMPS

Material

Steel (35CrMo), heat treated, black oxide finish, precision ground.

ping height.

Tips

Please apply grease to sliding surface.

Technical Notes

Cylindrical risers can be used to raise clam-

Order No.	h_1	Stroke s_1	l_1	d_1	d_2	h_2	h_3	h_4	w_1	w_2	r_1	r_2	Torque to Nm max.	A/F	Clamping force kN	Weight g
12552.W0221	35	10	19	M 8x1,25	M 8x30	49	12	6	10	22	20	15	20	22	7.9	125
12552.W0222	35	10	19	M 8x1,25	M 8x30	49	12	6	10	22	25	15	20	22	7.3	130
12552.W0223	35	10	19	M 8x1,25	M 8x30	49	12	6	10	22	30	15	20	22	6.7	135
12552.W0224	45	10	19	M 8x1,25	M 8x30	59	12	16	10	22	20	15	20	22	7.9	160
12552.W0225	45	10	19	M 8x1,25	M 8x30	59	12	16	10	22	25	15	20	22	7.3	165
12552.W0226	45	10	19	M 8x1,25	M 8x30	59	12	16	10	22	30	15	20	22	6.7	170
12552.W0321	50	15	30	M12x1,7 5	M12x4 5	77	16	10	18	32	40	26	45	36	13.5	450
12552.W0322	50	15	30	M12x1,7 5	M12x4 5	79	16	10	18	32	50	26	45	36	12.6	480
12552.W0323	50	15	30	M12x1,7 5	M12x4 5	79	16	10	18	32	60	26	45	36	11.7	520
12552.W0324	65	15	30	M12x1,7 5	M12x4 5	92	16	25	18	32	40	26	45	36	13.5	600
12552.W0325	65	15	30	M12x1,7 5	M12x4 5	94	18	25	18	32	50	26	45	36	12.6	630
12552.W0326	65	15	30	M12x1,7 5	M12x4 5	94	18	25	18	32	60	26	45	36	11.7	670
12552.W0361	50	15	30	M16x2	M16x5 5	86	21	10	22	36	40	26	60	36	13.4	630
12552.W0362	50	15	30	M16x2	M16x5 5	86	21	10	22	36	50	26	60	36	12.4	680
12552.W0363	50	15	30	M16x2	M16x5 5	86	21	10	22	36	60	26	60	36	12.0	740
12552.W0364	65	15	30	M16x2	M16x5 5	101	21	25	22	36	40	26	60	36	13.4	780
12552.W0365	65	15	30	M16x2	M16x5 5	101	21	25	22	36	50	26	60	36	12.4	830
12552.W0366	65	15	30	M16x2	M16x5 5	101	21	25	22	36	60	26	60	36	12.0	890