



**12550.4**

ADJUSTABLE VERTICAL CLAMPS

### Material

Steel (C45), black oxide finish.

### Tips

For use with hook clamps part no's 12550.W0010- .W0012 and 12554.

Order No.	Hook clamp size dia.	$h_1$	$l_1$	$d_1$	$d_2$ tol. f7	$h_2$	$h_3$	$d_3$	$d_4$	Torque to Nm max.	A/F	Weight g
<b>12550.W1101</b>	10	35	11	14	10 <sup>+0,1,0</sup>	16	13	M 4x0,7	M 6x1	2.7	12	30
<b>12550.W1121</b>	12	40	14	16	12 <sup>+0,1,0</sup>	19	14	M 6x1	M 8x1,25	7.0	13	45
<b>12550.W1181</b>	18	55	19	24	18	25	20	M 8x1,25	M 8x1,25	30	22	140
<b>12550.W1201</b>	20	63	30	32	20	30	21	M10x1,5	M12x1,75	38	30	400
<b>12550.W1202</b>	20	80	30	32	20	30	23	M10x1,5	M12x1,75	38	30	500
<b>12550.W1251</b>	25	80	30	40	25	40	25	M12x1,75	M12x1,75	50	36	600
<b>12550.W1252</b>	25	100	30	40	25	40	25	M12x1,75	M12x1,75	50	36	800
<b>12550.W1321</b>	32	80	30	50	32	40	25	M16x2	M16x2	80	46	930
<b>12550.W1322</b>	32	100	30	50	32	40	25	M16x2	M16x2	80	46	1230

