



12620.1

LOW PROFILE SIDE CLAMPING

Material

Body: steel (42CrMo), quenched and tempered, black oxide finish.

Handle shank: steel (C43), black oxide finish.

Ball knob: ABS resin, black.

Order No.	Type	s ₁	h ₁ ±0.01	h ₂	h ₃	d ₁	d ₂	d ₃	d ₄ tol. G6	d ₅ tol. H7	Weight g
12620.W0005	Clockwise	1.5	32	24.5	10	40	13.5	20	8	5	245
12620.W0105	Anti Clockwise	1.5	32	24.5	10	40	13.5	20	8	5	245
12620.W0008	Clockwise	2.0	40	30.7	13	50	18	25	12	8	470
12620.W0108	Anti Clockwise	2.0	40	30.7	13	50	18	25	12	8	470

Order No.	d ₆	d ₇	d ₈	r ₁	α	Recommended workpiece thickness tolerance	Clamping mechanism	Handle load N max.	Clamping force kN max.
12620.W0005	M4x8	M5x0.8	18	76.5	90°	±0,3	Spiral Cam, 4°	150	0.9
12620.W0105	M4x8	M5x0.8	18	76.5	90°	±0,3	Spiral Cam, 4°	150	0.9
12620.W0008	M6x9	M6x1	25	111.5	110°	±0,5	Spiral Cam, 4°	200	2.5
12620.W0108	M6x9	M6x1	25	111.5	110°	±0,5	Spiral Cam, 4°	200	2.5

