




12562.2

ADJUSTABLE VERTICAL CLAMPS

Material

Body, handle, clamping spindle: steel (C45), quenched and tempered, electroless nickel plated.

Arm, cam shaft: steel (42CrMo4), quenched

and tempered, electroless nickel plated.

Knob: phenolic plastic, black.

parenthesised values denote clamping height range.

Tips

Clamping height can be adjusted. The

Order No.	Clamping direction	Clamping height finished surface min.	Clamping height finished surface max.	Clamping height rough surface min.	Clamping height rough surface max.	h_1	h_2	h_3	h_4	h_5	h_6	l_1	l_2	Weight g
12562.W0330	Clockwise	22,8 (22,3~23,3)	24,8 (24,3~25,3)	22,4 (21,9~22,9)	24,4 (23,9~24,9)	49	45.8	30	10	22.8	6	18	26	112
12562.W0340	Clockwise	31,3 (30,6~32,0)	33,3 (32,6~34,0)	32,2 (31,5~32,9)	34,2 (33,5~34,9)	66	61.3	40	14	28.5	8	23	35	250
12562.W0350	Clockwise	32,5 (31,7~33,2)	39,0 (38,2~39,7)	33,5 (32,7~34,2)	40,0 (39,2~40,7)	82	76.5	50	18	45.5	12	30	45	570
12562.W0360	Clockwise	36,5 (35,5~37,4)	46,0 (45,0~46,9)	39,0 (38,0~39,9)	48,5 (47,5~49,4)	100	93.0	60	22	57.0	15	40	55	1200
12562.W0331	Counter Clockwise	22,8 (22,3~23,3)	24,8 (24,3~25,3)	22,4 (21,9~22,9)	24,4 (23,9~24,9)	49	45.8	30	10	22.8	6	18	26	112
12562.W0341	Counter Clockwise	31,3 (30,6~32,0)	33,3 (32,6~34,0)	32,2 (31,5~32,9)	34,2 (33,5~34,9)	66	61.3	40	14	28.5	8	23	35	250
12562.W0351	Counter Clockwise	32,5 (31,7~33,2)	39,0 (38,2~39,7)	33,5 (32,7~34,2)	40,0 (39,2~40,7)	82	76.5	50	18	45.5	12	30	45	570



Order No.	Clamping direction	Clamping height finished surface min.	Clamping height finished surface max.	Clamping height rough surface min.	Clamping height rough surface max.	h ₁	h ₂	h ₃	h ₄	h ₅	h ₆	l ₁	l ₂	Weight g
12562.W0361	Counter Clockwise	36,5 (35,5~37,4)	46,0 (45,0~46,9)	39,0 (38,0~39,9)	48,5 (47,5~49,4)	100	93.0	60	22	57.0	15	40	55	1200

Order No.	l ₃	l ₄	l ₅	d ₁	d ₂	d ₃	d ₄	d ₅	r ₁	w ₁	w ₂	w ₃	Clamping force kN max.	Clamping mechanism	Clamping stroke s ₁	Advance stroke s ₂	Operating load N max.
12562.W0330	22	6	11.5	18	15	4.3	27	M 4x0,70	50	36	8	4.3	1.1	Spiral Cam, Cam Angle 5°	1.0	0.8	100
12562.W0340	30	8	15.3	23	20	5.3	34	M 5x0,80	63	45	10	5.3	1.8	Spiral Cam, Cam Angle 5°	1.4	1.1	150
12562.W0350	37	8	20.7	30	26	8.4	48	M 8x1,25	80	65	16	8.4	2.2	Spiral Cam, Cam Angle 5°	1.5	1.4	200
12562.W0360	45	8	25.4	40	33	10.5	64	M10x1,50	100	85	20	10.4	3.5	Spiral Cam, Cam Angle 4°	1.9	1.7	300
12562.W0331	22	6	11.5	18	15	4.3	27	M 4x0,70	50	36	8	4.3	1.1	Spiral Cam, Cam Angle 5°	1.0	0.8	100
12562.W0341	30	8	15.3	23	20	5.3	34	M 5x0,80	63	45	10	5.3	1.8	Spiral Cam, Cam Angle 5°	1.4	1.1	150
12562.W0351	37	8	20.7	30	26	8.4	48	M 8x1,25	80	65	16	8.4	2.2	Spiral Cam, Cam Angle 4°	1.5	1.4	200
12562.W0361	45	8	25.4	40	33	10.5	64	M10x1,50	100	85	20	10.4	3.5	Spiral Cam, Cam Angle 4°	1.9	1.7	300