




Retractable Clamps with adjustable handle

Adjustable Vertical Clamps



12610.1

ADJUSTABLE VERTICAL CLAMPS

Material

Body/spindle: steel (C45), tempered and black oxide finish.
Arm/joint: steel (35CrMo), tempered and

black oxide finish.

Tips

Clamping height can be adjusted. The

values in brackets shows clamping height range. Screw clamping mechanism allows for longer clamping stroke and greater clamping force.

Order No.	h ₁	h ₂	h ₃	h ₄	h ₅	h ₆	l ₁	l ₂	l ₃	l ₄	Weight g
12610.W0006	81	45	10	24.0	8	47	18	25.5	20	25	242
12610.W0008	100	55	12	30.5	10	63	22	32.0	25	31	490

Order No.	l ₅	l ₆	r ₁	w ₁	w ₂	w ₃	w ₄	w ₅	d ₁	Handle load N max.	Clamping height finished surface min.	Clamping height finished surface max.	Clamping height rough surface min.	Clamping height rough surface max.	Clamping stroke s ₁	Clamping force kN max.	Clamping force mechanical max.
12610.W0006	16	11	40	42	26	22	32	M 6x1	5.5	170	32 (32,0~29,5)	40 (40,0~37,5)	35 (35,0~32,5)	43 (43,0~40,5)	2.5	2.4	Screw
12610.W0008	20	14	65	52	32	28	40	M 8x1, 25	6.5	210	37 (37,0~33,5)	48 (48,0~44,5)	42 (42~38,5)	53 (53,0~49,5)	3.5	4.2	Screw

Adjustable Vertical Clamps

Retractable Clamps with adjustable handle



ADJUSTABLE VERTICAL CLAMPS

