


Retractable Clamps with eccentric handle

Adjustable Vertical Clamps



12610.2

ADJUSTABLE VERTICAL CLAMPS

Material

Body/spindle: steel (C45), tempered and black oxide finish.

Arm/joint: steel (35CrMo), tempered and

black oxide finish.

Tips

Clamping height can be adjusted. The

values in brackets shows clamping height range.

Order No.	h_1	h_2	h_3	h_4	h_5	h_6	l_1	l_2	l_3	l_4	Weight g
12610.W0106	89	45	10	24.0	8	50	18	25.5	20	25	244
12610.W0108	109	55	12	30.5	10	63	22	32.0	25	31	468

Order No.	l_5	l_6	w_1	w_2	w_3	w_4	w_5	d_1	Handle load N max.	Clamping height finished surface min.	Clamping height finished surface max.	Clamping height rough surface min.	Clamping height rough surface max.	Clamping stroke s_1	Clamping force kN max.	Clamping mechanism	Overall stroke s_2
12610.W0106	16	11	42	26	22	32	M 6x1	5.5	100	32 (31,5~32,5)	40 (39,5~40,5)	35 (34,5~35,5)	43 (42,5~43,5)	1.0	0.7	Spiral Cam, 4°	1.5
12610.W0108	20	14	52	32	28	40	M 8x1, 25	6.5	150	37 (36,4~37,6)	48 (47,4~48,6)	42 (41,4~42,6)	53 (52,4~53,6)	1.2	1.1	Spiral Cam, 4°	1.8

Adjustable Vertical Clamps

Retractable Clamps with eccentric handle



ADJUSTABLE VERTICAL CLAMPS

