




Screw Jacks

plain Ø12 centering hole



Screw Jacks



15000

SCREW JACKS

Material

Body: carbon steel, enamelled.
Spindle: steel, tempered.
Trapezoidal thread, self-locking with end stop.

Technical Notes

Light duty: for clamps with slot widths up to 14mm.

Medium duty: for clamps with slot widths approx. 14-22mm.

Heavy duty: for clamps with slot widths between 20-40mm.

Extra heavy duty: for supporting larger work-pieces.

Tips

Centering hole Ø12mm in top of screw

jacks (no hole on part no. 15000.W0050).
When using in conjunction with forked clamps no. 10100, we recommend the use of locating pad no. 15060.
See technical pages for the table of locating pad and support pad elements suitability.

Order No.	Type	h_1 min.	h_2 max.	d_1	d_2	d_3	d_4	d_5	Static load kN max.	Weight g
15000.W0050	Light Duty	38	50	31	31	-	-	20x4	15	190
15000.W0052	Medium Duty	42	52	50	50	12	M38x2	30x4	60	550
15000.W0070	Medium Duty	50	70	50	50	12	M38x2	30x4	60	620
15000.W0100	Medium Duty	70	100	50	50	12	M38x2	30x4	60	900
15000.W0140	Heavy Duty	100	140	68	68	12	-	40x7	100	2760
15000.W0210	Heavy Duty	140	210	80	70	12	-	50x8	170	4600
15000.W0200	Extra Heavy	140	200	100	80	12	-	65x10	350	6900
15000.W0280	Extra Heavy	190	280	140	110	12	-	80x10	600	19000
15000.W0300	Extra Heavy	190	300	100	80	12	-	65x10	350	9000

