




# Clamping Pins for pull clamps

## Low Profile Side Clamping



**12620.3**

LOW PROFILE SIDE CLAMPING

### Material

Shank: steel (35CrMo), induction hardened (taper seat), precision ground.  
Head: steel (C45), tempered and black oxide finish.

### Technical Notes

The length  $l_3$  should be decided depending on the workpiece thickness, adjustable by  $\pm 1$ mm.

### Tips

In the order table replace XX with  $l_3$  length required to suit workpiece (in mm).

| Order No.      | $d_1$ | $d_2$<br>tol. f7 | $d_3$<br>tol. f7 | $d_4$ | $d_5$ | $d_6$   | $l_1$ | $l_2$ | $l_3$          | Weight<br>g |
|----------------|-------|------------------|------------------|-------|-------|---------|-------|-------|----------------|-------------|
| 12620.W0551-XX | 10    | 5                | 5                | 3     | M 3x4 | M 3x0,5 | 17    | 10    | $3 < l_3 < 50$ | 8~16        |
| 12620.W0552-XX | 10    | 6                | 5                | 3     | M 3x4 | M 3x0,5 | 17    | 10    | $3 < l_3 < 50$ | 8~19        |
| 12620.W0581-XX | 16    | 8                | 8                | 4.3   | M 5x5 | M 5x0,8 | 22    | 15    | $4 < l_3 < 80$ | 30~60       |
| 12620.W0582-XX | 16    | 10               | 8                | 4.3   | M 5x5 | M 5x0,8 | 22    | 15    | $4 < l_3 < 80$ | 31~77       |

