




Screw Jacks

aluminium base - plain Ø centering hole



Screw Jacks



15100

SCREW JACKS

Material

Body & base: aluminium 400 N/mm² tensile strength.
Spindle: steel, tempered.
Trapezoidal thread, self-locking with end stop.

Technical Notes

See technical pages for the table of loca-

ting pad and support locating element suitability.
Greater heights can be achieved by combining screw jacks with the centering support pad no. 15060.

Tips

The swarf is absorbed into the aluminium base thereby protecting the machine table.

Particularly useful for delicate machine tables and high precision machines.

Important Notes

Do not adjust screw jacks under load.

Order No.	Size	h_1 min.	h_1 max.	d_1	d_2	d_3	d_4	Static load kN max.	Weight g
15100.W0052	52	42	52	50	50	12	30x4	30	370
15100.W0070	70	50	70	50	50	12	30x4	30	430
15100.W0100	100	70	100	50	50	12	30x4	30	600