


Screw Jacks

aluminium - magnetic base



Screw Jacks



15120

SCREW JACKS

Material

Body: aluminium 400N/mm² tensile strength.
Base: magnetic.
Spindle: steel, tempered.
Trapezoidal thread, self locking with end stop.

Technical Notes

See technical pages for the table of locating pad and support locating element suitability.

Tips

Allows for positioning of screw jacks on

both horizontal and vertical surfaces.
Greater heights can be achieved by combining the screw jacks with the centering pad no. 15060<X\15060#22>.
Magnetic base ensures precise positioning of workpiece on vertical faces.

Order No.	Size	h_1 min.	h_1 max.	d_1	d_2	d_3	d_4	Static load kN max.	Weight g
15120.W0006	62	52	62	50	50	12	30x4	30	380
15120.W0008	80	60	80	50	50	12	30x4	30	550
15120.W0011	110	80	110	50	50	12	30x4	30	710