


Modular Screw Jack Base







15370.3

Material

Steel, tempered, burnished.

Technical Notes

Can be used on T-slots and grid plates by

means of adapters which are screwed in the base element. The individual elements are easily joined together with threaded ring ensuring process reliability.

Order No.	h_1	h ₂	h ₃	h ₄	h ₅	w_1	d_1	d_2	d_3	d_4	d_5	d_6	Weight
15370.W0236	86	36	30	37	27	6	90	M76x3	42.5	41	M16	6.2	1497



Modular Screw Jacks

how to use



With the modular screw jack your production becomes even more flexible and economical. When combined you can achieve a maximum height of 1620mm.

Benefits

- Maximum height of 1620mm.
- Quick set-up time.

The Elements

- 1 Bearing pads, 15374.W0075, 15374.W0175, 15374.W0275
- 2 Screwjack, 15370.W0040, 15372.W0023
- 3 Spacer, 15370.W0116, 15370.W0126, 15370.W0135
- 4 Base, 15370.W0236, 15370.W0356, 15370.W0456
- 5 Thread adapter 15374.W0016, 15374.W0020, 15374.W0024



SCREW JACKS