




## Compact Floating Clamps

separate clamping and locking



## Adjustable Vertical Clamps



# 12662.2

ADJUSTABLE VERTICAL CLAMPS

### Material

Body: steel case-hardened, nitrided, manganese phosphate treated and ground.  
Clamping jaws: steel case-hardened, nitrided, manganese phosphate treated.  
Housing: aluminium, blue anodised.

### Technical Notes

Used to clamp and support additional clamping points on extremely pliable work pieces, whilst minimising deformation of component. It also serves to reduce vibration during machining.

### Tips

Alternative clamping jaws available, see part 12660.W0050 to W0058 and 12660.W0148 to W0156.

Order No.	Description	Clamping & support force kN max.	Clamping stroke $s_1$	Weight g
12662.W0010	Clamping & Locking	8	0-12	1650