


# Modular Screw Jack Base



Screw Jacks



**15370.3**

SCREW JACKS

## Material

Steel, tempered, burnished.

## Technical Notes

Can be used on T-slots and grid plates by

means of adapters which are screwed in the base element. The individual elements are easily joined together with threaded ring ensuring process reliability.

Order No.	$h_1$	$h_2$	$h_3$	$h_4$	$h_5$	$w_1$	$d_1$	$d_2$	$d_3$	$d_4$	$d_5$	$d_6$	Weight g
<b>15370.W0236</b>	86	36	30	37	27	6	90	M76x3	42.5	41	M16	6.2	1497



With the modular screw jack your production becomes even more flexible and economical. When combined you can achieve a maximum height of 1620mm.

### Benefits

- Maximum height of 1620mm.
- Quick set-up time.

### The Elements

- ① Bearing pads, 15374.W0075, 15374.W0175, 15374.W0275
- ② Screwjack, 15370.W0040, 15372.W0023
- ③ Spacer, 15370.W0116, 15370.W0126, 15370.W0135
- ④ Base, 15370.W0236, 15370.W0356, 15370.W0456
- ⑤ Thread adapter  
15374.W0016, 15374.W0020, 15374.W0024

