


Modular Screw Jack Base adjustable



Screw Jacks



15370.4

SCREW JACKS

Material

Steel, tempered, burnished.

individual elements are easily joined together.

Technical Notes

Can be used on T-slots and grid plates. The

Enables easy positioning on a machine table.

Order No.	h_1	h_2	h_3	w_1	w_2	d_1	d_2	d_3	d_4	d_5	Weight g
15370.W0356	106	56	20	17	20	M76x3	90	42.5	200	150	5717



With the modular screw jack your production becomes even more flexible and economical. When combined you can achieve a maximum height of 1620mm.

Benefits

- Maximum height of 1620mm.
- Quick set-up time.

The Elements

- ① Bearing pads, 15374.W0075, 15374.W0175, 15374.W0275
- ② Screwjack, 15370.W0040, 15372.W0023
- ③ Spacer, 15370.W0116, 15370.W0126, 15370.W0135
- ④ Base, 15370.W0236, 15370.W0356, 15370.W0456
- ⑤ Thread adapter
15374.W0016, 15374.W0020, 15374.W0024

