


Clamping Jaws M16 for floating clamp

Adjustable Vertical Clamps



12664.2

ADJUSTABLE VERTICAL CLAMPS

Material

Steel case-hardened, nitrided, manganese phosphate treated.

Technical Notes

For use with 12664.1 clamps. A selection of alternative clamping jaws.

Order No.	Type	Clamping range	h_1	h_2	h_3	h_4	Weight g
12664.W0060	1	10-25	29.0	40	33.3	27.6	402
12664.W0062	2	0-14	41.0	40	33.3	27.6	380
12664.W0064	3	23-28	21.6	45	38.3	32.6	435
12664.W0066	4	35-50	18.6	54	47.3	41.6	490

