





# Adjustable Step Blocks with spiral gearing

## Screw Jacks



14040

SCREW JACKS

### Material

Steel, tempered and enamelled.

The tooth form is a metric profile to DIN 13 sheet 1 with a pitch of 2,5mm. It lies in the normal section of the setting level.

### Technical Notes

DIN 6326.

| Order No.   | Type  | Clamping height $h_1$<br>min. | Clamping height $h_1$<br>max. | Description | $h_2$ | $w_1$ | $l_1$ | Lower part | Upper part | Single parts | Weight<br>g |
|-------------|-------|-------------------------------|-------------------------------|-------------|-------|-------|-------|------------|------------|--------------|-------------|
| 14040.W0001 | A     |                               |                               | Lower part  | 42    | 60    | 80    |            |            | A            | 850         |
| 14040.W0002 | B     |                               |                               | Lower part  | 82    | 60    | 80    |            |            | B            | 2300        |
| 14040.W0003 | C     |                               |                               | Lower part  | 122   | 60    | 80    |            |            | C            | 3800        |
| 14040.W0004 | K     |                               |                               | Upper part  | 24    | 30    | 70    |            |            | K            | 200         |
| 14040.W0005 | G     |                               |                               | Upper part  | 44    | 30    | 70    |            |            | G            | 500         |
| 14040.W0014 | A+K   | 25                            | 45                            | Combination |       |       |       | A          | K          |              | 1050        |
| 14040.W0015 | A+G   | 45                            | 65                            | Combination |       |       |       | A          | G          |              | 1350        |
| 14040.W0017 | A+K+G | 25                            | 65                            | Combination |       |       |       | A          | KG         |              | 1550        |
| 14040.W0023 | B+K   | 65                            | 85                            | Combination |       |       |       | B          | K          |              | 2500        |
| 14040.W0025 | B+G   | 85                            | 105                           | Combination |       |       |       | B          | G          |              | 2800        |
| 14040.W0026 | B+K+G | 65                            | 105                           | Combination |       |       |       | B          | KG         |              | 3000        |
| 14040.W0034 | C+K   | 105                           | 125                           | Combination |       |       |       | C          | K          |              | 4000        |
| 14040.W0035 | C+G   | 125                           | 145                           | Combination |       |       |       | C          | G          |              | 4300        |
| 14040.W0036 | C+K+G | 105                           | 145                           | Combination |       |       |       | C          | KG         |              | 4500        |

