


Locating Pad - Pin Type for screw jacks





Material

Steel, hardened and blackened.

Tips

Can be used with screw jacks 15000 and

Order No.	d ₁	d ₂	d ₃	h ₁	h ₂	h ₃	Weight g
15040.W0163	63	14	12	15	12	8	310
15040.W0167	78	25	12	19	15	8	650

See technical pages for the table of screw

15300.

jack suitability.



15030 - 15090 **Clamping & Height Setting**

Wixroyd Screw Jacks, Locating and Support Elements



15030 Spherical

15040 Pin Type

15050



Centering Pin

Cylindrical

15080 Self-Aligning

> 15090 Pivot Ball



15042 Locating Pad



15002 Screw Jack



These screw and aligning jacks offer a broad range of applications. Due to their robust construction, the screw jacks function securely and precisely, with infinite adjustment even under heavy loads.

- Safe and reliable clamp supports for heights from 38 to 1250mm.
- Accurate and safe supporting and setting of any workpiece in various levels and heights.
- Aluminium screw jacks for delicate machine tables, surface plates and CMM tables.
 - Magnetic screw jacks for horizontal and vertical supporting and setting.

Table of Suitability for Screw Jack Attachments

Attachments	Suited to screw jacks with centering pin - plain bore	Suitable so	rew jack
15030		15200	14130
15040		15220	14140
15050		15000	15300
15060	🕨 🕺 🖉	15000	15320
15070		15100	15360
15080		15120	15500
15090			

Attachments	Suited to screw jacks with either / or centering pin - threaded	Suitable screw jack		
15042	M 12	15002.W0052 / W0070 / W0100		
15062	M 10	15320 15360		
15062	M 12	15002.W0052 / W0070 / W0100		
Attachments Base thread		Suitable screw jack		
15042		15000.W0052 / W0070 / W0100		
15062	M38 x 2	15000.W0052 / W0070 / W0100 15100		



ov-W15030-A-T-W15090-A-T-wixroyd-screw-jacks-locating-support-elements-lnh - Updated -24-10-2022

14140



