



19240

STANDARD MANUAL CLAMPING

Material

All parts are produced from tempered steel according to DIN or factory standards,

screw parts to strength class 8 or 10. Ideal for tool making, manufacturing and training facilities.

Order No.	Thread & Slot size	Step blocks 14000	T-Bolts 21000	Step clamps 10020	Weight kg
19240.W0014	M12 x 14	.W0002 x 4pcs .W0003 x 4pcs	50mm .W0141 x 2pcs 80mm .W0143 x 4pcs 125mm .W0144 x 4pcs	.W0014 x 2pcs .W0015 x 2pcs	10.0
19240.W0016	M14 x 16	.W0002 x 4pcs .W0003 x 4pcs	63mm .W0161 x 2pcs 100mm .W0162 x 4pcs 160mm .W0163 x 4pcs	.W0014 x 2pcs .W0015 x 2pcs	11.1
19240.W0018	M16 x 18	.W0002 x 4pcs .W0003 x 4pcs	63mm .W0181 x 2pcs 80mm .W0182 x 4pcs 160mm .W0184 x 4pcs	.W0018 x 2pcs .W0019 x 2pcs	15.2
Order No.	Studs 21100	Fixture nuts 24300	Extension nuts 24600	Dished washers 25700	
19240.W0014	100mm .W0124 x 2pcs	.W0112 x 6pcs	.W0112 x 2pcs	.W0112 x 6pcs	
19240.W0016	100mm .W0142 x 2pcs 160mm .W0143 x 2pcs	.W0114 x 6pcs	.W0114 x 2pcs	.W0114 x 6pcs	
19240.W0018	125mm .W0164 x 4pcs 200mm .W0166 x 2pcs	.W0116 x 6pcs	.W0116 x 4pcs	.W0116 x 6pcs	