




Cast Iron Tombstones semi-finished

Base Plates & Clamping



19500

BASE PLATES & CLAMPING ANGLES

Material

Cast iron (GG30).

Technical Notes

19510 is the less expensive welded version.

Order No.	$w_1 \times l_1$	w_2 ± 0.2	l_2	l_3 ± 0.2	l_4 ± 0.2	l_5 ± 0.2	d_1	h_1	h_2	s_1 ± 1	No. of holes n	For screw	Weight kg
19500.W0002	400x400	150	-	-	150	150	12	475	400	81	4	M12	150
19500.W0003	400x400	150	500	-	150	150	12	475	400	81	4	M12	173
19500.W0004	500x500	200	-	-	200	200	12	595	500	101	6	M12	284
19500.W0005	500x500	200	630	-	200	200	12	595	500	101	6	M12	334
19500.W0006	630x630	200	-	-	200	200	16	725	630	131	6	M16	470
19500.W0007	800x800	300	-	100	300	300	16	910	800	151	8	M16	745